


3in1 HD Endoscope



Y102

This endoscope camera adopts high quality material with widely compatibility which can support Android smart-phone/PC Computer/ Macbook computer. Featuring with mini camera head, adjustable LEDs, HD camera, it is a utility class equipment with the function of real-time video viewing, video recording and picture capturing which is a best tool for inspecting hard-to-reach or hard-to-see places, such as vehicle repairs, sewer inspection/maintenance, vent pipe inspection etc.

Product Specifications:

Camera: IP67 waterproof

Resolution: 1280 x 720, 640*480(8mm)

640 x 480(7/5.5mm)


Camera Diameter: 8/7/5.5mm

Light: adjustable LED light

Focal distance: 1.2Inch-3.2Inch

View angle: 70°

USB Port: Micro USB/Type-c/USB



Broad Compatibility, Plug and Play


USB port, directly plug the USB connector to the Windows XP/7/8/10 & Macbook OS computer, the you'r ready to use.

Convertible 3-in-1 USB, Type-C & Micro USB Design.



Windows:

Download the soft by the link:www.kkmoom.com/camera.rar, and Connect the camera to your computer. Then you can take photo and viedo.





MacBook:

– For MacBook OS, please use "Photo Booth" "QuickTime Player" "VLC(VideoLan Client)".

Android :

– For Android users, software can be downloaded.

1. Download the APP by the link: www.kkmoom.com/an97.apk also you can scan the QR code, OTG SEE you will available  Connect the camera, the software automatically starts.



QR code

2. Other third party general software can be downloaded from Google Play Store, such as "Camerfi, OTG VIEW".

notice!

Android Phone(Android 4.4+ system), and your phone supports OTG and UVC function.

-How to Check OTG? You can install a free app “USB OTG Checker”which provides a simple method to check.


-Not support Android 7.0+, iPhone IOS systems, Windows Phone, Blackberry, Motorola, LG, Galaxy S8, Google Pixel Smartphone.

Two kinds of wire can be Choiced:soft and semi-rigid cable.




Installation methods for three types of attachments-hook and mirror, magnet are same.

Hook on to the hole



Put on rubber ring



Package Includes:

- 1 * Mini USB Endoscope
- 1 * Small hook
- 1 * Magnet
- 1 * Side audition
- 1 * fixed set
- 1 * Manual

